



Base body Parallel shank, with through-coolant, 3×D, Type: 36



Order data

| | |
|--------------|---------------|
| Order number | 232245 36 |
| GTIN | 4045197658401 |
| Item class | 22G |

Description

Version:

For holes up to IT10 accuracy.
With internal cooling.

Straight fluted.

Note:

Further sizes available on request.
Through-coolant: yes
Number of cutting edges Z: 2
Dia. range D_c : 36 - 47 mm
Reach L_1 : 120.7 mm
Shank $\varnothing D_s$: 40 mm
Shank length L_s : 70 mm
Clamping screws: 232990 TX20

Technical description

| | |
|---------------------------|-------------|
| Shank $\varnothing D_s$ | 40 mm |
| Clamping screws | 232990 TX20 |
| Dia. range D_c | 36 - 47 mm |
| Reach L_1 | 120.7 mm |
| Shank length L_s | 70 mm |
| Number of cutting edges Z | 2 |
| Version | 3×D |

| | |
|-----------------|-----------------|
| Shank | ISO 9766 |
| Through-coolant | yes |
| Type of product | Indexable drill |

Accessories

| | |
|---|-------------|
| Torx® set of screws 10 pieces Drive TX15 | 232990 TX15 |
| Torx® set of screws 10 pieces Drive TX20 | 232990 TX20 |
| 8 mm blade with magnet with 1/4 inch bit holder overall length 50 mm | 659874 50 |
| Torque screwdriver with scale, to take interchangeable blades maximum torque 1600 cNm | 659906 1600 |
| PrecisionBit for Torx®, 1/4 inch E 6.3 Torx® profile TX20 | 674248 TX20 |
| Torque screwdriver with scale, to take interchangeable blades maximum torque 1600 cNm | 659957 1600 |