

Garant
GARANT Master Tap Alu machine tap, DLC, M: M10

Order data

Order number	131110 M10
GTIN	4067263829959
Item class	11I

Description
Version:

High-performance tap, specially developed for **aluminium and non-ferrous alloys**. **Extra-long clamping slots** and neck length for usable **thread depth up to 4×D**.

- **HSS-E-PM tool material for high cutting edge stability.**
- **Ultra-smooth DLC coating for wear resistance and avoidance of edge build-up.**
- **Extra-long flute geometry.**

Technical description

Tolerance class	ISO 2X 6HX
Thread type	M
Number of clamping slots	3
Thread Ø	10 mm
Thread pitch	1.5 mm
Thread size	M10
Number of cutting edges Z	3
Tapping hole Ø	8.5 mm
Standard	Works standard
Shank Ø D _s	10 mm
Shank square □	8 mm
Overall length L	115 mm

Thread depth	40 mm
Tool material	HSS E PM
Coating	DLC
Flank angle	60 degrees
Thread standard	DIN 13
Taper lead form	B
Shank	Plain shank with h9
Through-coolant	no
Application for type of drilling	up to 4×D for through holes
Cutting direction	right-hand
Type of threading tool	Machine tap for dynamic machining
Colour ring	yellow
Series	Master Tap
Type of product	Taps

User data

	Suitability	V _c	ISO code
Aluminium	suitable	35 m/min	N
Aluminium (short chipping)	suitable	32 m/min	N
Alu > 10% Si	suitable	20 m/min	N
PMMA acrylic	suitable only under restricted conditions	20 m/min	N
PA 66	suitable only under restricted conditions	18 m/min	N
PEEK	suitable	18 m/min	N
Cu	suitable	18 m/min	N
CuZn	suitable	25 m/min	N
Oil	suitable		
wet maximum	suitable		

wet minimum

suitable