

Garant
GARANT Master Tap Alu machine tap, DLC, M: M16

Order data

Order number	134260 M16
GTIN	4067263830436
Item class	11I

Description
Version:

High-performance tap, specially developed for **aluminium and non-ferrous alloys**. **Dynamic helical pitch** of the clamping slots ensure **optimum chip evacuation** and **process reliability**.

- **HSS-E-PM tool material** – for **high cutting edge stability**.
- **Ultra-smooth DLC coating** for **wear resistance and avoidance of edge build-up**.
- **Dynamic helical pitch of the flutes**.
- **Short lead chamfer form E**.

Technical description

Shank $\varnothing D_s$	12 mm
Thread depth	48 mm
Tolerance class	ISO 2X 6HX
Tapping hole \varnothing	14 mm
Number of cutting edges Z	3
Number of clamping slots	3
Thread type	M
Overall length L	125 mm
Shank square \square	9 mm
Tool material	HSS E PM
Standard	Works standard

Thread pitch	2 mm
Thread Ø	16 mm
Coating	DLC
Flank angle	60 degrees
Thread standard	DIN 13
Taper lead form	E
Helix angle	45 degrees
Shank	Plain shank with h9
Through-coolant	no
Application for type of drilling	up to 3×D for blind holes
Cutting direction	right-hand
Type of threading tool	Machine tap for dynamic machining
Helix angle characteristic	unequal spacing
Colour ring	yellow
Series	Master Tap
Type of product	Tap

User data

	Suitability	V _c	ISO code
Aluminium	suitable	35 m/min	N
Aluminium (short chipping)	suitable		
Alu > 10% Si	suitable		
PMMA acrylic	suitable only under restricted conditions	20 m/min	N
PA 66	suitable only under restricted conditions	18 m/min	N
PEEK	suitable	18 m/min	N
Cu	suitable	18 m/min	N
CuZn	suitable		

Oil	suitable
wet maximum	suitable
wet minimum	suitable