

**Garant**
**GARANT Master Tap Alu machine tap, DLC, M: M16**

**Order data**

Order number	131110 M16
GTIN	4067263829980
Item class	111

**Description**
**Version:**

**High-performance tap**, specially developed for **aluminium and non-ferrous alloys**. **Extra-long clamping slots** and neck length for usable **thread depth up to 4×D**.

- **HSS-E-PM tool material for high cutting edge stability.**
- **Ultra-smooth DLC coating for wear resistance and preventing galling.**
- **Extra-long flute geometry.**

Thread type: M

Tool material: HSS E PM

Standard: Works standard

Tolerance class: ISO 2X 6HX

Thread pitch: 2 mm

Overall length L: 135 mm

Shank Ø D<sub>s</sub>: 12 mm

Shank square □: 9 mm

Tapping hole Ø: 14 mm

**Technical description**

Overall length L	135 mm
Shank Ø D <sub>s</sub>	12 mm
Shank square □	9 mm
Number of clamping slots	3
Standard	Works standard
Thread type	M

Number of cutting edges Z	3
Tool material	HSS E PM
Thread size	M16
Tolerance class	ISO 2X 6HX
Thread depth	64 mm
Thread pitch	2 mm
Thread Ø	16 mm
Tapping hole Ø	14 mm
Coating	DLC
Flank angle	60°
Thread standard	DIN 13
Taper lead form	B
Shank	Plain shank with h9
Through-coolant	no
Application for type of drilling	up to 4×D for through holes
Cutting direction	right-hand
Type of threading tool	Machine tap for dynamic machining
Colour ring	yellow
Series	Master Tap
Type of product	Taps

## User data

	Suitability	V <sub>c</sub>	ISO code
Aluminium	suitable	35 m/min	N
Aluminium (short chipping)	suitable	32 m/min	N
Alu > 10% Si	suitable	20 m/min	N
PMMA acrylic	suitable only under restricted conditions	20 m/min	N

PA 66	suitable only under restricted conditions	18 m/min	N
PEEK	suitable	18 m/min	N
Cu	suitable	18 m/min	N
CuZn	suitable	25 m/min	N
Oil	suitable		
wet maximum	suitable		
wet minimum	suitable		