


Garant
GARANT Master eco screw-on toolholder short, left-hand, Shank / insert size: 20/11mm

Order data

| | |
|--------------|---------------|
| Order number | 261123 20/11 |
| GTIN | 4067263122562 |
| Item class | 21U |

Description
Version:

Highly efficient cooling directly on the cutting edge and additional flank face cooling.

Note:

Coolant transfer via slot on the underside of the shank in conjunction with GARANT Master eco toolholders No. 319006 – 319136 or No. 317900 for shank length < 125 mm. Optional connection possibility via hose connection (G 1/8 inch) No. 269207 and 269208.

Technical description

| | |
|---------------------------------|-----------------|
| Series | Master Eco |
| Insert size | 11 mm |
| Functional width L ₄ | 25 mm |
| suitable indexable insert | VB.. 1103.. |
| Pack of insert screws | 269023 1 |
| Head length L ₁ | 35 mm |
| ISO code toolholder | SVJBR/L 2020X11 |
| Overall length L | 95 mm |
| Shank size | 20 mm |
| Standard | Works standard |

| | |
|------------------------|-------------------------------|
| Application type | left-hand |
| Through-coolant | yes |
| Setting angle κ | 93 degrees |
| Application | External longitudinal turning |
| Application | External longitudinal turning |
| Type of product | Screw-on toolholder |