


Garant
GARANT Master Eco lever lock toolholder short, right-hand, Shank / insert size: 25/16mm

Order data

| | |
|--------------|---------------|
| Order number | 261136 25/16 |
| GTIN | 4067263122623 |
| Item class | 21U |

Description
Version:

Highly efficient cooling directly on the cutting edge and additional flank face cooling.

Note:

Coolant transfer via slot on the underside of the shank in conjunction with GARANT Master eco toolholders No. 319006 – 319136 or No. 317900 for shank length < 125 mm. Optional connection possibility via hose connection (G 1/8 inch) No. 269207 and 269208.

Technical description

| | |
|---------------------------------|-----------------|
| Head length L ₁ | 40 mm |
| Pack of insert screws | 269023 3 |
| Functional width L ₄ | 32 mm |
| ISO code toolholder | SVJCR/L 2525X16 |
| Shim screw | 269013 7 |
| Shank size | 25 mm |
| Insert size | 16 mm |
| Shim | 259033 5 |
| Series | Master Eco |
| Overall length L | 110 mm |

| | |
|---------------------------|-------------------------------|
| suitable indexable insert | VC.. 1604.. |
| Standard | Works standard |
| Application type | right-hand |
| Through-coolant | yes |
| Setting angle κ | 93 degrees |
| Application | External longitudinal turning |
| Application | External longitudinal turning |
| Type of product | Screw-on toolholder |