

Garant**GARANT Master Tap Alu machine tap, DLC, G: G3/4****Order data**

Order number	133260 G3/4
GTIN	4067263830214
Item class	111

Description**Version:**

High-performance tap, specially developed for **aluminium and non-ferrous alloys**.

- **HSS-E-PM tool material for high cutting edge stability**
- **Ultra-smooth DLC coating for wear resistance and avoidance of edge build-up**

Application:

For Whitworth parallel pipe threads DIN-ISO 228/1 (threads that do not form a seal within the connection).

Technical description

Shank \varnothing D _s	20 mm
Tool material	HSS E PM
Threads per inch	14
Shank square \square	16 mm
Thread pitch	1.814 mm
Thread depth	79.32 mm
Thread \varnothing	26.44 mm
Number of clamping slots	4
Tapping hole \varnothing	24.5 mm
Thread size	G3/4
Overall length L	140 mm

Number of cutting edges Z	4
Series	Master Tap
Coating	DLC
Thread type	G
Flank angle	55 degrees
Standard	DIN 5156
Tolerance class	ISO 228
Taper lead form	B
Shank	Plain shank with h9
Through-coolant	no
Application for type of drilling	up to 3×D for through holes
Cutting direction	right-hand
Type of threading tool	Machine tap for dynamic machining
Colour ring	yellow
Type of product	Taps

User data

	Suitability	V _c	ISO code
Aluminium	suitable	35 m/min	N
Aluminium (short chipping)	suitable	32 m/min	N
Alu > 10% Si	suitable	20 m/min	N
PMMA acrylic	suitable only under restricted conditions	20 m/min	N
PA 66	suitable only under restricted conditions	18 m/min	N
PEEK	suitable	18 m/min	N
Cu	suitable	18 m/min	N
CuZn	suitable	25 m/min	N
Oil	suitable		

wet maximum	suitable
wet minimum	suitable