

**Garant**
**GARANT Master Eco lever lock toolholder short, right-hand, Shank / insert size: 20/11mm**

**Order data**

Order number	261136 20/11
GTIN	4067263122609
Item class	21U

**Description**
**Version:**

Highly efficient cooling directly on the cutting edge and additional flank face cooling.

**Note:**

Coolant transfer via slot on the underside of the shank in conjunction with GARANT Master eco toolholders No. 319006 – 319136 or No. 317900 for shank length < 125 mm. Optional connection possibility via hose connection (G 1/8 inch) No. 269207 and 269208.

**Technical description**

Series	Master Eco
Overall length L	95 mm
Pack of insert screws	269023 1
Shank size	20 mm
Insert size	11 mm
ISO code toolholder	SVJCR/L 2020X11
Head length L <sub>1</sub>	35 mm
Functional width L <sub>4</sub>	25 mm
suitable indexable insert	VC.. 1103..
Standard	Works standard

Application type	right-hand
Through-coolant	yes
Setting angle $\kappa$	93 degrees
Application	External longitudinal turning
Application	External longitudinal turning
Type of product	Screw-on toolholder