

Garant
GARANT Master Tap SteelHT machine tap HSS-E-PM Form B 6HX, TiCN, M: M27

Order data

Order number	131940 M27
GTIN	4067263829645
Item class	11l

Description
Version:

High-performance tap, specially developed for use in **steels with high tensile strength** and for **difficult-to-machine materials**. **Strong spiral point**, for process stability at high cutting forces.

- **HSS-E-PM tool material – for very high cutting edge stability.**
- **Optimised honed cutting edges.**
- **TiCN coating – for maximum wear protection.**

Recommendation:

For **TOOLOX and HARDOX materials we recommend deviating from the DIN data** (see table) by **selecting a larger tapping hole \varnothing** .

Thread type: M

Tool material: HSS E PM

Standard: DIN 376

Tolerance class: ISO 2X 6HX

Thread pitch: 3 mm

Overall length L: 160 mm

Shank $\varnothing D_s$: 20 mm

Shank square \square : 16 mm

Tapping hole \varnothing : 24 mm

Technical description

Thread type	M
Shank square \square	16 mm
Tapping hole \varnothing	24 mm

Standard	DIN 376
Tolerance class	ISO 2X 6HX
Thread size	M27
Thread Ø	27 mm
Shank Ø D _s	20 mm
Thread pitch	3 mm
Overall length L	160 mm
Number of cutting edges Z	4
Number of clamping slots	4
Thread depth	81 mm
Tool material	HSS E PM
Coating	TiCN
Flank angle	60°
Thread standard	DIN 13
Taper lead form	B
Shank	Plain shank with h9
Through-coolant	no
Application for type of drilling	up to 3×D for through holes
Cutting direction	right-hand
Type of threading tool	Machine tap for dynamic machining
Colour ring	red
Series	Master Tap
Type of product	Tap

User data

	Suitability	V _c	ISO code
Steel < 750 N/mm ²	suitable only under restricted conditions	30 m/min	P
Steel < 900 N/mm ²	suitable	20 m/min	P

Steel < 1100 N/mm ²	suitable	15 m/min	P
Steel < 1400 N/mm ²	suitable		
Steel < 50 HRC	suitable only under restricted conditions		
TOOLOX 33	suitable	15 m/min	H
TOOLOX 44	suitable		
HARDOX 500 < 1600 N/mm ²	suitable only under restricted conditions		
INOX > 900 N/mm ²	suitable		
Ti > 850 N/mm ²	suitable only under restricted conditions		
Oil	suitable		
wet maximum	suitable		