


**Garant****CNMG 160612, Grade: HB7130-2**

### Order data

Order number	250170 HB7130-2
GTIN	4067263290605
Item class	21G

### Description

CNMG 160612 HB7130-2 Grade: HB7130-2  
Chip breaker: VM  
Tolerance: M  
Cutting depth  $a_p$ : 0.5 - 4 mm  
Feed  $f$ : 0.1 - 0.4 mm/rev.  
Cutting speed  $v_c$  main application: 70 - 240 m/min

### Technical description

Coating	coated
Chip breaker	VM
Number of changes/inserts	4
Cutting depth $a_p$	0.5 - 4 mm
Tool material	Carbide
Corner radius	1.2 mm

Finishing/roughing assignment	Finishing
Cutting speed $v_c$ main application	70 - 240 m/min
Feed $f$	0.1 - 0.4 mm/rev.
Main application	M
ISO code indexable insert	CNMG 160612
Cutting conditions	slightly interrupted
Grade	HB7130-2
Tolerance	M
Type of product	Indexable insert for turning