

Garant
KNUX 160410R, Grade: HB7130-2

Order data

Order number	251036 HB7130-2
GTIN	4067263330226
Item class	21G

Description

KNUX 160410R HB7130-2 Grade: HB7130-2

Chip breaker: VM

Chip diverter: 2.2 mm

Cutting depth a_p : 0.5 - 5 mm

Feed f : 0.2 - 0.5 mm/rev.

Cutting speed v_c main application: 70 - 240 m/min

Technical description

Number of changes/inserts	2
Chip diverter	2.2 mm
Cutting speed v_c main application	70 - 240 m/min
Finishing/roughing assignment	Finishing
Chip breaker	VM
Main application	M
Grade	HB7130-2
Cutting depth a_p	0.5 - 5 mm
Coating	coated
Feed f	0.2 - 0.5 mm/rev.

Corner radius	1 mm
Cutting conditions	continuous
Tool material	Carbide
ISO code indexable insert	KNUX 160410R
Type of product	Indexable insert for turning