


Garant**SNMG 120412, Grade: HB7130-2**

Order data

Order number	251226 HB7130-2
GTIN	4067263290827
Item class	21G

Description

SNMG 120412 HB7130-2 Corner radius: 1.2 mm
Grade: HB7130-2
Chip breaker: VM
Cutting depth a_p : 0.5 - 4 mm
Feed f : 0.1 - 0.4 mm/rev.
Cutting speed v_c main application: 70 - 240 m/min

Technical description

Finishing/roughing assignment	Finishing
Cutting depth a_p	0.5 - 4 mm
Coating	coated
Corner radius	1.2 mm
Chip breaker	VM
Grade	HB7130-2
Cutting speed v_c main application	70 - 240 m/min

Cutting conditions	slightly interrupted
Main application	M
Tool material	Carbide
Number of changes/inserts	8
ISO code indexable insert	SNMG 120412
Feed f	0.1 - 0.4 mm/rev.
Type of product	Indexable insert for turning