


**Garant**
**SNMG 120404, Grade: HB7130-2**


## Order data

Order number	251222 HB7130-2
GTIN	4067263330257
Item class	21G

## Description

SNMG 120404 HB7130-2 Corner radius: 0.4 mm  
 Grade: HB7130-2  
 Chip breaker: VM  
 Cutting depth  $a_p$ : 0.5 - 4 mm  
 Feed  $f$ : 0.1 - 0.4 mm/rev.  
 Cutting speed  $v_c$  main application: 70 - 240 m/min

## Technical description

Number of changes/inserts	8
Chip breaker	VM
Grade	HB7130-2
Cutting depth $a_p$	0.5 - 4 mm
Tool material	Carbide
Corner radius	0.4 mm
Cutting conditions	slightly interrupted

Cutting speed $v_c$ main application	70 - 240 m/min
Coating	coated
Finishing/roughing assignment	Finishing
Main application	M
ISO code indexable insert	SNMG 120404
Feed $f$	0.1 - 0.4 mm/rev.
Type of product	Indexable insert for turning