

**Garant**
**TCMT 16T308, Grade: HB7130-2**

**Order data**

Order number	260958 HB7130-2
GTIN	4067263291008
Item class	21G

**Description**

TCMT 16T308 HB7130-2 Grade: HB7130-2  
 Chip breaker: VS  
 Cutting depth  $a_p$ : 0.2 - 1.5 mm  
 Feed  $f$ : 0.1 - 0.3 mm/rev.  
 Cutting speed  $v_c$  main application: 80 - 270 m/min

**Technical description**

ISO code indexable insert	TCMT 16T308
Finishing/roughing assignment	Finishing
Grade	HB7130-2
Corner radius	0.8 mm
Tool material	Carbide
Cutting depth $a_p$	0.2 - 1.5 mm
Cutting conditions	slightly interrupted
Feed $f$	0.1 - 0.3 mm/rev.

Coating	coated
Main application	M
Cutting speed $v_c$ main application	80 - 270 m/min
Number of changes/inserts	3
Chip breaker	VS
Type of product	Indexable insert for turning