

**Garant****TCMT 110208, Grade: HB7130-2**

### Order data

Order number	260954 HB7130-2
GTIN	4067263290995
Item class	21G

### Description

TCMT 110208 HB7130-2 Grade: HB7130-2  
Chip breaker: VS  
Cutting depth  $a_p$ : 0.2 - 1.5 mm  
Feed  $f$ : 0.1 - 0.3 mm/rev.  
Cutting speed  $v_c$  main application: 80 - 270 m/min

### Technical description

Chip breaker	VS
Number of changes/inserts	3
Finishing/roughing assignment	Finishing
Cutting speed $v_c$ main application	80 - 270 m/min
Tool material	Carbide
ISO code indexable insert	TCMT 110208
Main application	M
Cutting depth $a_p$	0.2 - 1.5 mm

Corner radius	0.8 mm
Cutting conditions	slightly interrupted
Grade	HB7130-2
Coating	coated
Feed f	0.1 - 0.3 mm/rev.
Type of product	Indexable insert for turning