

**Garant**
**GARANT Master Mute boring bar, right-hand, Shank  $\varnothing$  / insert size: 12/11mm**

**Order data**

Order number	260920 12/11
GTIN	4067263623120
Item class	29E

**Description**
**Version:**

Round shank without clamping face.

**Note:**

Do not clamp on the area marked S!

**Technical description**

Minimum pre-drill $\varnothing D_{\min}$	16 mm
Overall length L	120 mm
ISO code toolholder	A12X STFPCR/L11
Overhang $L_1$	60 mm
Shank $\varnothing D_s$	12 mm
Centre offset $L_3$	9 mm
Setting angle $\kappa$	90 degrees
Pack of insert screws	269028 38
Series	Master Mute
suitable indexable insert	TC.. 1102..
Insert size	11 mm
non-clamping range S	72 mm
Standard	DIN 8024
Application type	right-hand

Vibration	damped
Through-coolant	yes
Application	Internal longitudinal turning
Type of product	Boring bar