

Garant
DNMG 150604, Grade: HB7140-2


Order data

Order number	250658 HB7140-2
GTIN	4067263315056
Item class	21G

Description

DNMG 150604 HB7140-2 Grade: HB7140-2
 Chip breaker: VS
 Cutting depth a_p : 0.3 - 2 mm
 Feed f : 0.1 - 0.4 mm/rev.
 Cutting speed v_c main application: 70 - 230 m/min

Technical description

Main application	M
Feed f	0.1 - 0.4 mm/rev.
Cutting conditions	heavily interrupted
Coating	coated
Cutting speed v_c main application	70 - 230 m/min
Grade	HB7140-2
Finishing/roughing assignment	Finishing

Corner radius	0.4 mm
Number of changes/inserts	4
Cutting depth a_p	0.3 - 2 mm
Tool material	Carbide
Chip breaker	VS
ISO code indexable insert	DNMG 150604
Type of product	Indexable insert for turning