



## LED floodlight with dimmer function CONNECT, Type: NOVA-2



### Order data

Order number	081232 NOVA-2
GTIN	5708997006719
Item class	07A

### Description

**Version:**

Scangrip CONNECT work lamps are based on the CAS system and are also compatible with 18-V batteries from all leading power tool manufacturers.

High-performance cordless LED floodlight with dimmer function. The housing is made of injection-moulded aluminium and is extremely robust and

resistant to strong blows, impacts and vibrations. For use with CAS 12 V and 18 V

Batteries, 18-V batteries from leading power tool manufacturers or direct connection to the SCANGRIP®

Power supply.

**Function:**

IP30: Protected against penetration by foreign bodies with  $\varnothing > 2.5$  mm. However, tools and wires should be kept away and there is no protection against water.

**Supplied with:**

Lamps are supplied without battery and charger.

**Note:**

Suitable batteries, chargers and power supply units for wired power supply can be found under 073870 &ndash; 073890 and 081249.

### Technical description

Type of rechargeable battery	Lithium-ion
Battery voltage	12 V
Battery voltage	18 V
Number of rechargeable batteries contained	0
Power supply	Mains operated
Illumination	200 - 2000 lm
IP Index of Protection	IP 30
Overall length	163 mm
Overall height	163 mm
Overall width	63 mm
Type of product	Floodlight