

**Garant**
**GARANT Master eco clamp toolholder, right-hand, Shank / insert size: 20/08mm**

**Order data**

Order number	251914 20/08
GTIN	4067263122333
Item class	21U

**Description**
**Version:**

Highly efficient cooling directly on the cutting edge and additional flank face cooling.

**Note:**

Coolant transfer via slot on the underside of the shank in conjunction with GARANT Master eco toolholders No. 319006 – 319136 or No. 317900 for shank length < 125 mm. Optional connection possibility via hose connection (G 1/8 inch) No. 269207 and 269208.

**Technical description**

Insert size	8 mm
Head length L <sub>1</sub>	35 mm
Shim	259033 6
ISO code toolholder	DWLNR/L 2020K08
Clamp, screw, spring	259036 25
suitable indexable insert	WN.. 0804..
Series	Master Eco
Overall length L	125 mm
Shim screw	259027 9
Shank size	20 mm

Functional width $L_4$	25 mm
Standard	Works standard
Application type	right-hand
Through-coolant	yes
Setting angle $\kappa$	95 degrees
Application	External longitudinal turning
Application	External longitudinal turning
Type of product	Screw-on toolholder