

Garant

GARANT Master eco clamp toolholder, left-hand, Shank / insert size: 25/08mm



Order data

Order number	251915 25/08
GTIN	4067263122364
Item class	21U

Description

Version:

Highly efficient cooling directly on the cutting edge and additional flank face cooling.

Note:

Coolant transfer via slot on the underside of the shank in conjunction with GARANT Master eco toolholders No. 319006 – 319136 or No. 317900 for shank length < 125 mm. Optional connection possibility via hose connection (G 1/8 inch) No. 269207 and 269208.

Technical description

Shim screw	259027 9
ISO code toolholder	DWLNR/L 2525M08
Functional width L ₄	32 mm
Head length L ₁	35 mm
Shank size	25 mm
Series	Master Eco
Clamp, screw, spring	259036 26
Shim	259033 6
Overall length L	150 mm
suitable indexable insert	WN.. 0804..
Insert size	8 mm

Standard	Works standard
Application type	left-hand
Through-coolant	yes
Setting angle κ	95 degrees
Application	External longitudinal turning
Application	External longitudinal turning
Type of product	Screw-on toolholder