


Garant
CNMG 160608, Grade: HB7130-2


Order data

Order number	250334 HB7130-2
GTIN	4067263290629
Item class	21G

Description

CNMG 160608 HB7130-2 Grade: HB7130-2
 Chip breaker: VG
 Cutting depth a_p : 1.5 - 6 mm
 Feed f : 0.25 - 0.6 mm/rev.
 Cutting speed v_c main application: 60 - 220 m/min

Technical description

Finishing/roughing assignment	Roughing
Cutting conditions	slightly interrupted
Chip breaker	VG
Number of changes/inserts	4
ISO code indexable insert	CNMG 120412
Grade	HB7130-2
Cutting depth a_p	1.5 - 6 mm

Tool material	Carbide
Corner radius	1.2 mm
Main application	M
Coating	coated
Feed f	0.25 - 0.6 mm/rev.
Cutting speed v_c main application	60 - 220 m/min
Type of product	Indexable insert for turning