

Garant**DNMG 110408, Grade: HB7130-2**

Order data

Order number	250654 HB7130-2
GTIN	4067263329992
Item class	21G

Description

DNMG 110408 HB7130-2 Grade: HB7130-2
Chip breaker: VS
Cutting depth a_p : 0.3 - 2 mm
Feed f : 0.1 - 0.4 mm/rev.
Cutting speed v_c main application: 80 - 270 m/min

Technical description

Grade	HB7130-2
Cutting conditions	slightly interrupted
Coating	coated
Tool material	Carbide
Cutting depth a_p	0.3 - 2 mm
Main application	M
Feed f	0.1 - 0.4 mm/rev.

Corner radius	0.8 mm
Number of changes/inserts	4
Finishing/roughing assignment	Finishing
Chip breaker	VS
Cutting speed v_c main application	80 - 270 m/min
ISO code indexable insert	DNMG 110408
Type of product	Indexable insert for turning