


Garant
KNUX 160410L, Grade: HB7130-2

Order data

Order number	251038 HB7130-2
GTIN	4067263330233
Item class	21G

Description

KNUX 160410L HB7130-2 Grade: HB7130-2
 Chip breaker: VM
 Chip diverter: 2.2 mm
 Cutting depth a_p : 0.5 - 5 mm
 Feed f : 0.2 - 0.5 mm/rev.
 Cutting speed v_c main application: 70 - 240 m/min

Technical description

Finishing/roughing assignment	Finishing
Grade	HB7130-2
Feed f	0.2 - 0.5 mm/rev.
Chip breaker	VM
Chip diverter	2.2 mm
Cutting speed v_c main application	70 - 240 m/min
Cutting depth a_p	0.5 - 5 mm
Coating	coated
Number of changes/inserts	2
Main application	M

Cutting conditions	continuous
Tool material	Carbide
Corner radius	1 mm
ISO code indexable insert	KNUX 160410L
Type of product	Indexable insert for turning