

Garant**TNMG 160408, Grade: HB7130-2**

Order data

Order number	251434 HB7130-2
GTIN	4067263290834
Item class	21G

Description

TNMG 160408 HB7130-2 Grade: HB7130-2
Chip breaker: VS
Cutting depth a_p : 0.3 - 2 mm
Feed f : 0.1 - 0.4 mm/rev.
Cutting speed v_c main application: 80 - 270 m/min

Technical description

Cutting speed v_c main application	80 - 270 m/min
Feed f	0.1 - 0.4 mm/rev.
Coating	coated
Main application	M
Tool material	Carbide
Corner radius	0.8 mm
Cutting conditions	slightly interrupted
Finishing/roughing assignment	Finishing

Chip breaker	VS
Number of changes/inserts	6
ISO code indexable insert	TNMG 160408
Grade	HB7130-2
Cutting depth a_p	0.3 - 2 mm
Type of product	Indexable insert for turning