

Garant**VC.T 160402, Grade: HB7140-2**

Order data

Order number	261370 HB7140-2
GTIN	4067263329893
Item class	21G

Description

VC.T 160402 HB7140-2 Grade: HB7140-2
Chip breaker: VS
Tolerance: M
Cutting depth a_p : 0.2 - 1.5 mm
Feed f : 0.1 - 0.3 mm/rev.
Cutting speed v_c main application: 70 - 230 m/min

Technical description

Coating	coated
Number of changes/inserts	2
Grade	HB7140-2
Chip breaker	VS
Feed f	0.1 - 0.3 mm/rev.
Tolerance	M

Cutting speed v_c main application	70 - 230 m/min
Finishing/roughing assignment	Finishing
Main application	M
Corner radius	0.2 mm
Cutting depth a_p	0.2 - 1.5 mm
Tool material	Carbide
ISO code indexable insert	VCMT 160402
Cutting conditions	heavily interrupted
Type of product	Indexable insert for turning