




Internal precision bore gauge KT, Measuring range: 100-510mm



Order data

Order number	435125 100-510
GTIN	2050002074408
Item class	46D

Description

Version:

Two-point dial bore gauge, based on the **Schwenk version**. For measuring internal profiles and splines, serrations and splined hub profiles. High accuracy and reliability due to segment deflection of the contact point travel. Wide measurement range covered by interchangeable measuring tips. The measuring inserts have an internal thread for fitting ball tips. The carbide balls on the spherical tips are available from $\varnothing 0.5\text{mm}$ in 0.001 mm increments (tolerance $< 2\mu\text{m}$).

Supplied with:

Gauge holder with probe rods and measuring tips, without spherical tips and display unit.

Optional extras:

Spherical inserts with carbide balls, precision dial comparator No. 434674, inductive precision dial comparator No. 434670, dial indicator with anticlockwise scale 434807 size 10, digital dial indicator 434322.

Note:

Version as a plug gauge for quicker and more reliable measuring without fluctuation.

Technical description

Measurement depth	235 mm
Number of measuring discs	4
Repetition accuracy without dial gauge	0.5 μm
Measuring range	100 - 510 mm

Number of contact points	5
Packaging	sturdy box
Calibration	Price on request
Type of product	2-point precision bore gauge