

Garant
TCMT 110208, Grade: HB7140-2


Order data

| | |
|--------------|-----------------|
| Order number | 260954 HB7140-2 |
| GTIN | 4067263329626 |
| Item class | 21G |

Description

TCMT 110208 HB7140-2 Grade: HB7140-2
 Chip breaker: VS
 Cutting depth a_p : 0.2 - 1.5 mm
 Feed f : 0.1 - 0.3 mm/rev.
 Cutting speed v_c main application: 70 - 230 m/min

Technical description

| | |
|--------------------------------------|---------------------|
| Tool material | Carbide |
| Finishing/roughing assignment | Finishing |
| Cutting conditions | heavily interrupted |
| Cutting speed v_c main application | 70 - 230 m/min |
| Main application | M |
| Cutting depth a_p | 0.2 - 1.5 mm |
| ISO code indexable insert | TCMT 110208 |
| Feed f | 0.1 - 0.3 mm/rev. |

| | |
|---------------------------|------------------------------|
| Grade | HB7140-2 |
| Coating | coated |
| Corner radius | 0.8 mm |
| Chip breaker | VS |
| Number of changes/inserts | 3 |
| Type of product | Indexable insert for turning |