

Garant**VC.T 160404, Grade: HB7140-2**

Order data

| | |
|--------------|-----------------|
| Order number | 261372 HB7140-2 |
| GTIN | 4067263329909 |
| Item class | 21G |

Description

VC.T 160404 HB7140-2 Grade: HB7140-2
Chip breaker: VS
Tolerance: M
Cutting depth a_p : 0.2 - 1.5 mm
Feed f : 0.1 - 0.3 mm/rev.
Cutting speed v_c main application: 70 - 230 m/min

Technical description

| | |
|--------------------------------------|---------------------|
| Cutting depth a_p | 0.2 - 1.5 mm |
| Chip breaker | VS |
| Cutting conditions | heavily interrupted |
| Corner radius | 0.4 mm |
| Cutting speed v_c main application | 70 - 230 m/min |
| Tool material | Carbide |

| | |
|-------------------------------|------------------------------|
| Main application | M |
| Feed f | 0.1 - 0.3 mm/rev. |
| Grade | HB7140-2 |
| Tolerance | M |
| ISO code indexable insert | VC.T 160404 |
| Coating | coated |
| Finishing/roughing assignment | Finishing |
| Number of changes/inserts | 2 |
| Type of product | Indexable insert for turning |