



## High feed rate milling cutter 7792VX, with threaded shank, Ø D / number of teeth Z: 32/3mm



### Order data

Order number	221905 32/3
GTIN	2050002058538
Item class	28R

### Description

#### Description:

The unique design of the indexable inserts together with their approach angle in the milling body greatly reduces the radial forces and diverts them into the axial direction. Particularly thick indexable inserts with 4 cutting edges for the heaviest duties and high cost-effectiveness. The tool has particular advantages for face milling and milling deep pockets. With its ground wiper chamfer it is equally well suited also to plunge milling and finish milling operations.

### Technical description

maximum cutting depth $a_{p\max}$	1.5 mm
Ø D <sub>3</sub>	17 mm
Mounting thread M	M16
suitable indexable insert	XD.. 0904
Overall length L <sub>tot</sub>	43 mm
Cutting edge Ø D <sub>c</sub>	32 mm
Indexable insert size	09
Insert screw	229918 (T15; 2.1 Nm)
Number of cutting edges Z	3
Through-coolant	yes

Ramping length L for $\alpha_{\max}$	16.3 mm
Circular interpolation milling $\varnothing D_{\min}$	49 mm
Ramping angle $\alpha_{\max}$	0.88 degrees
Circular interpolation milling $\varnothing D_{\max}$	62 mm
Shank type	with threaded shank
Milling application	Ramping
Milling application	Circular milling
Milling application	Plunging
Machining strategy	HPC
Type of product	Copy mill

---

## Accessories

Clamping screw	229918
----------------	--------