



LED cordless lamp 0 version without battery, 12 V, Type: M12UCL



Order data

| | |
|--------------|---------------|
| Order number | 073210 M12UCL |
| GTIN | 4058546361501 |
| Item class | 07A |

Description

Version:

Robust Li-Ion battery lights with high light intensity. LED work lamp and assembly lamp.

- **With swivel joint, adjustable 300° horizontally and 180° vertically.**
- **Magnetic base and large magnetic storage.**

Suitable for:

Milwaukee 12 V batteries MB12.

Supplied with:

Cordless lamp without battery and without charger.

Technical description

| | |
|--|----------------|
| Illumination | 1200 lm |
| Power supply | Mains operated |
| Illumination step 2 | 800 lm |
| Manufacturer's designation | M12 UCL |
| Number of rechargeable batteries contained | 0 |
| Battery voltage | 12 V |
| Type of rechargeable battery | Lithium-ion |
| Bulb | LED module |

| | |
|--|-----------------------|
| Illumination step 3 | 600 lm |
| Product name attribute | 12 V |
| suitable battery - supplier / battery type / voltage | Milwaukee type B 12 V |
| Type of product | Work lamp |