



## HOLEX Pro Inox solid carbide high-performance drill, plain shank DIN 6535 HA, AlTiN, Ø DC m7: 2,8mm



### Order data

Order number	122685 2,8
GTIN	4067263005131
Item class	12F

### Description

#### Version:

Efficient drilling especially for use in **stainless and acid-resistant steels**. Straight main cutting edges with **optimised cutting edge design** for improved chip breaking behaviour. Enlarged flutes for **excellent chip evacuation**. Increased wear resistance due to **improved carbide substrate** and **high temperature resistant coating**.

#### Note:

Flute length  $L_c = L_2 + 1.5 \times D_c$ .

HB and HE shanks are available at the same price as HA.

For **HB shanks**: use order **no. 122686**.

For **HE shanks**: use order **no. 122687**.

### Technical description

Tolerance nominal Ø	m7
Overall length L	55 mm
Nominal Ø D <sub>c</sub>	2.8 mm
Standard	DIN 6537
Number of cutting edges Z	2
Flute length L <sub>c</sub>	22.5 mm
Feed f in stainless steel < 900 N/mm <sup>2</sup>	0.04 mm/rev.
Shank Ø D <sub>s</sub>	4 mm
recommended maximum drilling depth L <sub>2</sub>	18.3 mm

Series	Pro Inox
Coating	AlTiN
Tool material	Solid carbide
Version	6xD
Point angle	140 degrees
Shank	DIN 6535 HA to h6
Through-coolant	yes, with 25 bar
Colour ring	blue
Type of product	Twist Drill

### User data

	Suitability	V <sub>c</sub>	ISO code
Aluminium (short chipping)	suitable only under restricted conditions	140 m/min	N
Alu > 10% Si	suitable only under restricted conditions	120 m/min	N
Steel < 500 N/mm <sup>2</sup>	suitable	120 m/min	P
Steel < 750 N/mm <sup>2</sup>	suitable	110 m/min	P
Steel < 900 N/mm <sup>2</sup>	suitable	90 m/min	P
Steel < 1100 N/mm <sup>2</sup>	suitable	80 m/min	P
INOX < 900 N/mm <sup>2</sup>	suitable	55 m/min	M
INOX > 900 N/mm <sup>2</sup>	suitable	45 m/min	M
Ti > 850 N/mm <sup>2</sup>	suitable	35 m/min	S
wet maximum	suitable		
wet minimum	suitable only under restricted conditions		