



## HOLEX Pro INOX solid carbide high-performance drill, plain shank DIN 6535 HA, AlTiN, Ø DC m7: 15,2mm



### Order data

Order number	122390 15,2
GTIN	4067263003724
Item class	12F

### Description

#### Version:

Efficient drilling especially for use in **stainless and acid-resistant steels**.

Straight main cutting edges with **optimised cutting edge design** for improved chip breaking behaviour. Enlarged flutes for **excellent chip evacuation**. Increased wear resistance due to **improved carbide substrate** and **high temperature resistant coating**.

#### Note:

Flute length  $L_c = L_2 + 1.5 \times D_c$ .

HB and HE shanks are available at the same price as HA.

For **HB shanks**: use order **no. 122391**.

For **HE shanks**: use order **no. 122392**.

### Technical description

recommended maximum drilling depth $L_2$	41.8 mm
Shank $\varnothing D_s$	16 mm
Tolerance nominal $\varnothing$	m7
Feed $f$ in stainless steel $< 900 \text{ N/mm}^2$	0.16 mm/rev.
Nominal $\varnothing D_c$	15.2 mm
Overall length $L$	115 mm
Standard	DIN 6537 K
Number of cutting edges $Z$	2
Flute length $L_c$	65 mm

Series	Pro Inox
Coating	AlTiN
Tool material	Solid carbide
Version	4xD
Point angle	140 degrees
Shank	DIN 6535 HA to h6
Through-coolant	no
Colour ring	blue
Type of product	Twist Drill

### User data

	Suitability	V <sub>c</sub>	ISO code
Aluminium (short chipping)	suitable only under restricted conditions	140 m/min	N
Alu > 10% Si	suitable only under restricted conditions	120 m/min	N
Steel < 500 N/mm <sup>2</sup>	suitable	80 m/min	P
Steel < 750 N/mm <sup>2</sup>	suitable	75 m/min	P
Steel < 900 N/mm <sup>2</sup>	suitable	65 m/min	P
INOX < 900 N/mm <sup>2</sup>	suitable	35 m/min	M
INOX > 900 N/mm <sup>2</sup>	suitable	30 m/min	M
wet maximum	suitable		
wet minimum	suitable only under restricted conditions		