



HOLEX Pro INOX solid carbide high-performance drill, plain shank DIN 6535 HA, AlTiN, Ø DC m7: 6,7mm



Order data

Order number	122390 6,7
GTIN	4067263003175
Item class	12F

Description

Version:

Efficient drilling especially for use in **stainless and acid-resistant steels**.

Straight main cutting edges with **optimised cutting edge design** for improved chip breaking behaviour. Enlarged flutes for **excellent chip evacuation**. Increased wear resistance due to **improved carbide substrate** and **high temperature resistant coating**.

Note:

Flute length $L_c = L_2 + 1.5 \times D_c$.

HB and HE shanks are available at the same price as HA.

For **HB shanks**: use order **no. 122391**.

For **HE shanks**: use order **no. 122392**.

Technical description

Nominal Ø D_c	6.7 mm
Overall length L	79 mm
Feed f in stainless steel < 900 N/mm ²	0.09 mm/rev.
Standard	DIN 6537 K
Flute length L_c	34 mm
recommended maximum drilling depth L_2	24 mm
Tolerance nominal Ø	m7
Number of cutting edges Z	2
Shank Ø D_s	8 mm

Series	Pro Inox
Coating	AlTiN
Tool material	Solid carbide
Version	4xD
Point angle	140 degrees
Shank	DIN 6535 HA to h6
Through-coolant	no
Colour ring	blue
Type of product	Twist Drill

User data

	Suitability	V _c	ISO code
Aluminium (short chipping)	suitable only under restricted conditions	140 m/min	N
Alu > 10% Si	suitable only under restricted conditions	120 m/min	N
Steel < 500 N/mm ²	suitable	80 m/min	P
Steel < 750 N/mm ²	suitable	75 m/min	P
Steel < 900 N/mm ²	suitable	65 m/min	P
INOX < 900 N/mm ²	suitable	35 m/min	M
INOX > 900 N/mm ²	suitable	30 m/min	M
wet maximum	suitable		
wet minimum	suitable only under restricted conditions		