

Garant
Face mill arbor with cooling channel bore Form ADB, BT 30 A = 100, Spigot Ø d1: 22mm

Order data

Order number	303012 22
GTIN	4067263002666
Item class	31A

Description
Version:

Taper shank, spigots, and contact surfaces ground on collar.
All shanks hard turned (for smooth running!). Balancing quality G2.5 / 25,000 rpm. Form ADB.
With 4 cooling channel bores.

Supplied with:

Lock screw.

Optional extras:

Pull studs (PS) No. 308760 – 308802. Special toggle spanner No. 309840.

Technical description

Suitable toggle spanner No. 309840	22
Spigot Ø d ₁	22 mm
External Ø D	48 mm
Spare milling cutter lock screw No. 309860 / 309861	22
Adapter	BT 30 A = 100
Standard	DIN 6357
Arbor standard	ISO 7388-2
Arbor standard	JIS B6339

Shape	ADB
Balance quality G at rotational speed	G 2.5 at 25,000 rpm
Concentricity	$\leq 5 \mu\text{m}$
Machining strategy	HPC
Type of product	Face mill arbor