



TRIBOS-Mini-SVL extension cylindrical, Clamping $\varnothing D1$: 3mm



Order data

Order number	302383 3
GTIN	2050002076877
Item class	33U

Description

Version:

By using TRIBOS SVL extensions, standard cutting tools can be used instead of expensive special tools. The extension with concentricity of < 0.003 mm and a slender interference contour can be combined with a wide variety of chucks. The TRIBOS SVL extensions have already been proven for use in the medical, watch and jewellery industries, as well as in the automotive and electronics industries.

Advantage:

- **Optimised interference contour – ideal for bores in low-lying areas, e.g. in fixture construction.**
- **Axial length adjustment – length adjustment in the range of 0.01 mm accuracy, with adjustment travel of 10 mm.**
- **For the smallest diameters from 0.3 mm – economical for the most delicate machining operations without special tools.**
- **Flexible to use – suitable for hydraulic chucks and ER collet chucks.**
- **All commercially available shank types can be mounted (HA, HB, HE).**
- **Excellent vibration damping – avoidance of micro break-outs, top workpiece surfaces, less stress on the headstock, increase to tool life and thus reduction in costs.**
- **High speeds possible – up to 52,000 rpm.**

Function:

The TRIBOS SVP clamping devices make the polygon-shaped clamping diameter of the extension round and the tool shank can be easily inserted. If the pressure on the clamping diameter decreases, it becomes polygonal again and clamps the inserted tool shank reliably and accurately.

Optional extras:

TRIBOS-Mini clamping device No. 302384, TRIBOS-Mini SVP assembly jig No. 302386.

Technical description

Length L	100 mm
L ₁	24 mm
External Ø D	11 mm
Shank Ø D _s	12 mm
L ₂	22.5 mm
Ø D ₂	9 mm
Clamping Ø D ₁	3 mm
Through-coolant	yes
Balance quality G at rotational speed	G 2.5 at 25,000 rpm
Concentricity	≤ 3 µm
Machining strategy	HSC
Type of product	Extension