



Chain lever hoist BRAVO™ with round steel link chain, Safe working load: 0,25 t



Order data

Order number	086014 0,25
GTIN	2050001741967
Item class	08Y

Description

Version:

Hoist with **sheet steel casing**, extremely low weight, with **chain release as standard, low height, rotatable** bearing, forged hook. Exceptionally compact hoist (installed length 240 mm).

Application:

Versatile hoist for use even under the most difficult conditions.

Note:

The principle of the **threaded load pressure brake** is that the axial braking force is generated by the load itself and is thus proportional to the weight of the load. The load is safely held in all positions; to lower it, the difference between the braking torque and load torque must be overcome. All Yale all-purpose hoists are equipped with this device.

The automatic **chain release** permits **quick run-out** of the unloaded chain; when the load is applied, the **threaded load pressure brake** automatically takes effect again and the load is safely held.

The **slip clutch** (optional feature) prevents unduly high loading, and thus increases the working life of the lifting gear.

Hoists with overload protection (slip clutch) available on request.

minimum length between hooks: 240 mm

Standard lifting height: 1.5 m

Number of chains: 1

Safe working load: 250 kg
Weight: 2.4 kg

Technical description

Number of chains	1
Standard lifting height	1.5 m
minimum length between hooks	240 mm
Safe working load	250 kg
Housing material	Steel
Chain release.	yes
Safe working load in t	0.25 t
Weight	2.4 kg
Type of product	Lever hoist / chain pull