

Garant
Indexable drill combination shank Shank Ø 20 mm, 3×D, Ø DC m7: 24,5mm


Order data

Order number	232302 24,5
GTIN	4045197351852
Item class	21S

Description

Version:

High stability and very high process reliability.

With **shank Ø 20 mm**, particularly suitable for **driven tools** (see Group 31).

Application:

For stationary and rotating application.

For holes free of withdrawal scoring and exact dimensional accuracy (approx. ± 0.1 mm).

Also suitable for machines with low drive power. Especially for **MTC (Multi Task Cutting)** use on the new generation of turning/milling centres (**MTM**).

With indexable inserts No. 232400 – 232780.

Suitable for:

Inserts WOEX 040304.

Note:

Counterboring tools with up to 2 steps to your specification available on request. (Minimum order quantity: 2 pieces).

The enquiry form can be found in the eShop on the product page under "Forms".

CAUTION!

A disc falls off when the drill exits.

Risk of injury if the component is rotating.

Please take safety precautions.

Technical description

Reach L_1	75 mm
Pack of insert screws	239700 6IP1 (1.0 Nm)
Shank Ø D_s	20 mm

Number of cutting edges Z	1
ISO code indexable insert	WOEX 040304
Shank length L _s	50 mm
Nominal Ø D	24.5
Overall length L	149 mm
Maximum adjustment limit V _{max}	0.5 mm
Overhang L _A	99 mm
Drill depth for indexable insert drill up to	3×D
Shank	DIN 6535 HE, DIN 6595
Use for drilling	Centre drilling
Use for drilling	oblique spot drilling
Use for drilling	limited cross-drilling
Use for drilling	Aperture
Use for drilling	oblique exit
Use for drilling	convex
Through-coolant	yes
Machining strategy	MTC
Type of product	Indexable drill

Accessories

Torque screwdriver, fixed setting set torque 1,0 N·m	211750 1,0
Torx Plus® insert screw set 10 pieces Drive 6IP1	239700 6IP1
PrecisionBit for Torx Plus®, 1/4 inch E 6.3 Torx Plus® profile 6IP	674252 6IP