




## Indexable milling cutter 90° MEW, Plain shank, Ø D / number of teeth Z: 25/2mm



### Order data

Order number	225200 25/2
GTIN	4960664648252
Item class	250

### Description

#### Version:

Cost-efficient due to 4 cutting edges.

### Technical description

Indexable insert size	15
maximum cutting depth $a_{p\max}$	15 mm
Shank Ø $D_s$ h6	25 mm
Cutting edge Ø $D_c$	25 mm
suitable indexable insert	LOMU..
Insert screw	229714 (15IP; 3.5 Nm)
Overhang $L_1$	32 mm
Overall length $L_{\text{tot}}$	120 mm
Number of cutting edges Z	2
Shank type	Plain shank
Setting angle $\kappa$	90 degrees
Milling application	End milling
Milling application	Plunging
Through-coolant	yes

Type of product

End / face mill

---

## Accessories

Clamping screw

229714