



## Indexable milling cutter 90° MEW, with bore, $\varnothing D$ / number of teeth Z: 63/5mm



### Order data

Order number	225210 63/5
GTIN	4960664648696
Item class	250

### Description

**Version:**  
Cost-efficient due to 4 cutting edges.

### Technical description

suitable indexable insert	LOMU..
Insert screw	229714 (15IP; 3.5 Nm)
Mounting bore $\varnothing$	22 mm
maximum cutting depth $a_{p\max}$	15 mm
Indexable insert size	15
Cutting edge $\varnothing D_c$	63 mm
Overall length $L_{\text{tot}}$	40 mm
Number of cutting edges Z	5
Shank type	with bore
Setting angle $\kappa$	90 degrees

Milling application	End milling
Milling application	Plunging
Through-coolant	yes
Type of product	End / face mill

---

## Accessories

Clamping screw	229714
----------------	--------