

**Garant**
**Face mill arbor Form AD, BT 40 A = 100, Spigot Ø d1: 32mm**


## Order data

Order number	303810 32
GTIN	4067263014058
Item class	31A

## Description

### Version:

All shanks hard turned (for smooth running!). With RFID/Balluffchip bore and cooling channel bores.

### Advantage:

**The double contact between the taper** and the flat flange creates a more stable and precise clamping situation:

- **Better surface quality**
- **Longer tool life times**
- **Consistent seating in the headstock (even at high speeds)**
- **Smaller radial run-out**

A BT double contact arbor can also be used in a standard BT machine spindle – and vice versa. The advantages of the double contact are however achieved only when a double contact arbor and double contact spindle are used together.

### Supplied with:

Lock screw.

### Optional extras:

Pull studs (PS) No. 308760 – 308806. Special toggle spanner No. 309840.

## Technical description

Spigot Ø d <sub>1</sub>	32 mm
Suitable toggle spanner No. 309840	32

Spare milling cutter lock screw No. 309860 / 309861	32
a	1 mm
External Ø D	78 mm
Overhang dimension A	100 mm
Adapter	BT 40 A = 100
Standard	DIN 6357
Arbor standard	ISO 7388-2
Arbor standard	JIS B6339
Shape	AD
Cooling channel bore	not pluggable
Balance quality G at rotational speed	G 2.5 at 25,000 rpm
Concentricity	≤ 5 µm
Machining strategy	HPC
Version	BT-DC
Type of product	Face mill arbor