



Indexable milling cutter 90° MFWN, with bore, Ø D / number of teeth Z: 63/5mm



Order data

Order number	225615 63/5
GTIN	4960664647743
Item class	250

Description

Version:

Milling cutter with double-sided indexable inserts.

The combination of approach angle, chip chamber design as well as the geometries and cutting angles of the indexable inserts ensure outstanding metal removal rates, chip clearance, working life, and low cutting forces, and hence high cost-effectiveness.

Technical description

maximum cutting depth $a_{p\max}$	8 mm
Overall length L_{tot}	40 mm
suitable indexable insert	WNMU 0806..
Insert screw	229700 (T15; 4.2 Nm)
Mounting bore Ø	22 mm
Cutting edge Ø D_c	63 mm
Number of cutting edges Z	5

Shank type	with bore
Setting angle κ	90 degrees
Milling application	End milling
Milling application	Plunging
Through-coolant	yes
Type of product	End / face mill

Accessories

Clamping screw	229700
----------------	--------