



Indexable milling cutter 90° MEW, with bore, Ø D / number of teeth Z: 50/5mm



Order data

Order number	225210 50/5
GTIN	4960664648658
Item class	250

Description

Version:
Cost-efficient due to 4 cutting edges.

Technical description

Mounting bore Ø	22 mm
maximum cutting depth $a_{p,max}$	10 mm
Cutting edge Ø D_c	50 mm
Overall length L_{tot}	40 mm
suitable indexable insert	LOMU..
Insert screw	229713 (8IP; 1.2 Nm)
Indexable insert size	10
Number of cutting edges Z	5
Shank type	with bore
Setting angle κ	90 degrees

Milling application	End milling
Milling application	Plunging
Through-coolant	yes
Type of product	End / face mill

Accessories

Clamping screw	229713
----------------	--------