

Garant
Circular mill, Steel, Type: 12

Order data

Order number	217250 12
GTIN	4045197542663
Item class	21Q

Description
Note:

The actual groove depth S_{max} is calculated as follows: $(D-d_1) / 2$.

Tool exchange: PowerCard

Through-coolant: yes

for insert type: P12

smallest hole $\varnothing D$: 9.6 - 11.7 mm

Internal $\varnothing d_1$: 7 mm

maximum cutting depth S_{max} : 2.35 mm

Overhang L_1 : 22 mm

Overall length L_{tot} : 69.5 mm

Technical description

Shank type	Weldon
smallest hole $\varnothing D$	9.6 - 11.7 mm
Overall length L_{tot}	69.5 mm
Internal $\varnothing d_1$	7 mm
Overhang L_1	22 mm
maximum cutting depth S_{max}	2.35 mm
Set of insert screws	219832 (8IP; 1.0 Nm)
Shank $\varnothing D_s$ h6	12 mm
for insert type	P12

Through-coolant	yes
Thread depth	20 mm
Material of milling tool	Steel
Tool exchange	PowerCard
Type of product	Circular mills

Accessories

Set of insert screws 10-piece	219818
Set of insert screws 10-piece	219832