



Side clamp with cam, Thread: M10



Order data

| | |
|--------------|---------------|
| Order number | 370051 M10 |
| GTIN | 4059245559732 |
| Item class | 37K |

Description

Advantage:

- **Compact design.**
- **Quick and easy clamping of components with pull-down.**

Application:

For lateral clamping of narrow and wide workpieces. Clamping force is introduced by eccentric adjustment with an additional pull-down effect.

Material:

Housing made of tempered steel, gunmetal finished.

Technical description

| | |
|---------------------------|-------|
| maximum tightening torque | 55 Nm |
| Width B ₁ | 40 mm |
| Width B ₂ | 12 mm |
| Clamping range | 5 mm |
| Height H | 29 mm |
| Length L | 54 mm |

| | |
|-----------------|------------|
| Clamping force | 5.5 kN |
| Type of product | Side clamp |