

Garant

FeedKing high feed rate indexable face mill, with threaded shank, Ø D / number of teeth Z: 35/3mm



Order data

Order number	212905 35/3
GTIN	4045197320896
Item class	210

Description

Version:

Dynamic cutting edge geometry for highest feed rates. Extremely smooth cutting due to **self-stabilising insert bedding**. **Optimised geometry** for reduced cutting forces, thereby reducing the stress on the main spindle.

Advantage:

Particularly cost-effective due to **exceptionally sturdy 4-edge** inserts.

Note:

When working with extensions, always use internal cooling. Use GARANT torque screwdriver TQ No. **211750 size 3.8** with bit No. **674252 size 15IP**.

Technical description

Overall length L_{tot}	42 mm
Pack of insert screws	219933 (15IP; 3.8 Nm)
Ø D_1 h6	17 mm
Mounting thread M	M16
maximum cutting depth $a_{p\ max}$	1.15 mm
Cutting edge Ø D_c	35 mm
suitable indexable insert	XD.. 09T308

Ø D ₂	28.7 mm
Ø D ₃	19 mm
Number of cutting edges Z	3
Through-coolant	yes
Ramping length L for α_{\max}	18.5 mm
Circular interpolation milling Ø D _{min}	54 mm
Circular interpolation milling a _p	1.15 mm
Ramping angle α_{\max}	0.93 degrees
Circular interpolation milling Ø D _{max}	68 mm
Series	FeedKing
Shank type	with threaded shank
Milling application	Ramping
Milling application	Plunging
Milling application	Circular milling
Spacing of the cutters	unequal spacing
Machining strategy	HPC
Tool exchange	PowerCard
Type of product	Copy mill

Accessories

Torque screwdriver, fixed setting set torque 3,8 N·m	211750 3,8
Set of insert screws 10 pieces	219933
PrecisionBit for Torx Plus®, 1/4 inch E 6.3 Torx Plus® profile 15IP	674252 15IP