

Garant
Solid carbide milling cutter, Diamond, Ø f8 DC: 8mm

Order data

Order number	209713 8
GTIN	4045197512512
Item class	11Y

Description
Version:

With the latest generation of **crystalline diamond coating sp³**, for process reliability in machining **fibre-reinforced composites, CRP, GRP, and graphite.**

Dynamic cutter geometry.
Technical description

Cutting edge Ø D _c	8 mm
Feed f _z for slot milling in GRP CRP	0.05 mm
Overhang length L ₁ incl. recess	25 mm
Recess Ø D ₁	7.8 mm
Corner chamfer width at 45°	0.2 mm
No. of teeth Z	4
Feed f _z for slot milling in graphite	0.05 mm
Shank Ø D _s	8 mm
Overall length L	63 mm
Flute length L _c	19 mm
Direction of infeed	horizontal, oblique and vertical
Shank	DIN 6535 HA with h6
Tolerance nominal Ø	f8

Balance quality with shank	G 2.5 with HA
Helix angle	45 degrees
Corner chamfer angle	45 degrees
Coating	Diamond
Tool material	Solid carbide
Standard	Manufacturer's standard
Spacing of the cutters	unequal spacing
Cutting width a_e for milling operation	Full slot cutting depth $1 \times D$
Through-coolant	no
Colour ring	black
Type of product	End / face mill

User data

	Suitability	V_c	ISO code
PVDF GF20	suitable	200 m/min	N
POM GF25	suitable	190 m/min	N
PA 66 GF30	suitable	170 m/min	N
PEEK GF30	suitable	150 m/min	N
PTFE CF25	suitable	180 m/min	N
PEEK CF30	suitable	160 m/min	N
Hybrids	suitable		
Honeycomb sandwich	suitable	350 m/min	N
GRP	suitable	190 m/min	N
GRP, CRP	suitable	190 m/min	N
Graphite	suitable	340 m/min	N
wet minimum	suitable		
dry	Suitable		
Air	suitable		

Services

Shank grinding Type HB

129100 HB