

Garant
180° reverse countersinking mill, maximum countersink Ø D: 57mm

Order data

Order number	217180 57
GTIN	4045197465726
Item class	210

Description
Version:

With just one cutter (z = 1).

Note:

Dimension e = programming dimension (information on the end face). Use GARANT torque screwdriver TQ No. **211750 size 5.5** with bit No. **674252 size 20IP**.

Technical description

Shank type	Weldon
Number of cutting edges Z	1
L ₃	120 mm
Programming dimension e	9.55 mm
Countersink Ø D	57 mm
Minimum Ø d _{min}	39 mm
Shank Ø D _s h6	40 mm
Overhang L ₁	150 mm
Pack of insert screws	219848 (20IP; 5.5 Nm)
suitable indexable insert	260158
Through-coolant	yes
Overall length L	220 mm

Tool exchange	PowerCard
Type of product	Counterbores, countersinks

Accessories

Clamping screw	219945
Set of insert screws 10 pieces	219848