




## Safety shut-off Hose connection, Hose connection internal Ø (nominal bore): 13mm



### Order data

Order number	080287 13
GTIN	7391390285638
Item class	08A

### Description

#### Version:

**Steel couplings** have many advantages in pneumatic systems compared to standard brass couplings:

- **Easy to use with only one hand with low coupling force.**
- **High flow rates as a consequence of very low pressure drop.**
- **Long working life due to surface treatment and hardened components with tight manufacturing tolerances.**
- **Cost-effectiveness – the amortisation time is 2years at the most.**

The **eSafe safety coupling** satisfies the ISO standard 4414 and EN 983 It is first depressurised and then decoupled in a second step (no whiplash). New improved single-handed operation. Rate of flow: 2250 ltr/min, maximum operating pressure 16 bar.

#### Application:

For improving the performance, economics, and safety of industrial compressed air installations.

#### Note:

**The CEJN series 320 satisfies Euro standard 7.6 (nominal Ø 7.6 mm, Euro profile) and is compatible with all popular systems.**

### Technical description

Material	Steel coupling
Flow rate	2250 l/min
Hose connection internal Ø (nominal bore)	13 mm

maximum operating pressure	16 bar
Type of product	Coupling