



Indexable milling cutter 90° MEC11T, Plain shank, Ø D / number of teeth Z: 16/2Lmm



Order data

Order number	227300 16/2L
GTIN	4960664396030
Item class	250

Description

Description:

MEC11T mill type with higher stability due to lower number of cutters than MECX. This enables higher feed rates per cutter.

Note:

Without internal cooling.

Technical description

suitable indexable insert	BD.. 11T3
Overhang L_1	23 mm
Shank Ø D_s h6	12 mm
Insert screw	229708 (T8; 1.2 Nm)
maximum cutting depth $a_{p\max}$	10 mm
Cutting edge Ø D_c	16 mm
Overall length L_{tot}	100 mm
Number of cutting edges Z	2
Ramping length L for α_{\max}	9 mm
Circular interpolation milling Ø D_{\max}	30 mm
Circular interpolation milling Ø D_{\min}	26 mm
Ramping angle α_{\max}	1.27 degrees

Ø D ₃	10 mm
Shank type	Plain shank
Setting angle κ	90 degrees
Milling application	End milling
Milling application	Ramping
Milling application	Circular milling
Through-coolant	yes
Type of product	End / face mill

Accessories

Clamping screw	229708
----------------	--------