



## Indexable milling cutter 90° MEC11T, Plain shank, Ø D / number of teeth Z: 20/2XLmm



### Order data

Order number	227300 20/2XL
GTIN	4960664460984
Item class	250

### Description

#### Description:

MEC11T mill type with higher stability due to lower number of cutters than MECX. This enables higher feed rates per cutter.

### Technical description

suitable indexable insert	BD.. 11T3
Shank Ø D <sub>s</sub> h6	18 mm
Overall length L <sub>tot</sub>	170 mm
Insert screw	229708 (T8; 1.2 Nm)
maximum cutting depth a <sub>p max</sub>	10 mm
Overhang L <sub>1</sub>	30 mm
Cutting edge Ø D <sub>c</sub>	20 mm
Number of cutting edges Z	2
Ramping length L for α <sub>max</sub>	13 mm
Circular interpolation milling Ø D <sub>max</sub>	38 mm
Circular interpolation milling Ø D <sub>min</sub>	34 mm
Ramping angle α <sub>max</sub>	0.88 degrees
Ø D <sub>3</sub>	14 mm

Shank type	Plain shank
Setting angle $\kappa$	90 degrees
Milling application	End milling
Milling application	Ramping
Milling application	Circular milling
Through-coolant	yes
Type of product	End / face mill

---

## Accessories

Clamping screw	229708
----------------	--------